

## Спецификация G1000

- Material: metal+plastic.
- Image sensor: 2M fine quality image sensor
- Magnifications: 50x, 1000x
- Display: 4.3 inches TFT panel, 16:9
- Focusing range: 0-40mm
- Focus mode: manual
- Resolution: 1920\*1080, 1280\*960, 640\*480
- Micro TF card slot: support Micro TF card (not equipped with this unit) up to 32GB, including FAT, FAT32 two file formats
- Data format: JPG/AVI
- Light source: 8 LED lights (adjustable brightness)
- Frame rate: 30fps
- Interface: USB2.0
- Lens structure: 2G+IR
- Aperture: F4.5
- Lens angle: 16
- Power supply: 1 \* lithium battery, 3.7V, 1500mAh (included)
- Power source: DC 5V
- Battery continuous working time: about 4 hours
- Charging time: about 4 hours
- Stand size: 156 \* 122mm
- Package size: 210 \* 210 \* 135mm
- Package weight: 714g