


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1501761020](#)
Status: **Active**
Overview: [EconoLatch® Wire-to-Wire Interconnects](#)
Description: [EconoLatch® Plug Housing, Single Row, with Panel Mount Latch, 2 Circuits](#)

Documents:

Drawing (PDF)	Test Summary 1501760001-TS-000 (PDF)
Product Specification 1501760001-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 1501760001-AS-000 (PDF)	Product Literature (PDF)
Packaging Specification PK-150176-001-001 (PDF)	



Series image - Reference only

Agency Certification

UL E29179

General

Product Family	Crimp Housings
Series	150176
Application	Power, Wire-to-Wire
Overview	EconoLatch® Wire-to-Wire Interconnects
Product Literature Order No	987651-5541
Product Name	EconoLatch®
UPC	889056490252

Physical

Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-2
Gender	Plug
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.242/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	3.68mm
Pitch - Termination Interface	3.68mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	1501760001-AS-000
Packaging Specification	PK-150176-001-001
Product Specification	1501760001-PS-000
Sales Drawing	SD-150176-001-000
Test Summary	1501760001-TS-000

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[150176](#) Series

Mates With

EconoLatch® Receptacle Housing [150178](#)

Use With

EconoLatch® Male Terminal [150180](#)