



TYPE 1

**SPECIFICATIONS**

Current Rating: 3A AC,DC  
 Voltage Rating: 250V AC,DC  
 Temperature Range: -25°C ~ +85°C  
 Contact Resistance: 10mΩ Max  
 Insulation Resistance: 1000MΩ Min  
 Withstanding Voltage: 800V AC/minute  
 Pin Material: Brass/Tin-plated  
 Material: Nylon 66,UL94V-0  
 Color: Natural(White)

**Ordering Information & Dimensions**

PART NO.	Dimensions	
	A	B
A2502WR-02P1	2.50	7.50
A2502WR-03P1	5.00	10.00
A2502WR-04P1	7.50	12.50
A2502WR-05P1	10.00	15.00
A2502WR-06P1	12.50	17.50
A2502WR-07P1	15.00	20.00
A2502WR-08P1	17.50	22.50
A2502WR-09P1	20.00	25.00
A2502WR-10P1	22.50	27.50
A2502WR-11P1	25.00	30.00
A2502WR-12P1	27.50	32.50
A2502WR-13P1	30.00	35.00
A2502WR-14P1	32.50	37.50
A2502WR-15P1	35.00	40.00

				UNIT SCALE SHEET mm 1 of 1		TITLE:  <b>2.50mm PITCH 90° WAFER, TYPE 1</b>
				DRAWN BY 李勤 2006.05.14 APPROVED BY 董正一 2006.05.14		
		GENERAL TOLERANCE		ANGLE±		DRAW NO. : A2502WR-XP1
A0	NEW RELEASE	2006.05.14	X. X±0.25			
REV.	DESCRIPTION	DATE	X. XX±0.15			
			X. XXX±0.05			