



P/N LEGEND

A2502 WV-XP N O X T1 N XX G									
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩
① Series No.	② Connector type: WV=Vertical	③ No. of circuits	④ N=Halogen Free	⑤ Material: 0=Nylon 66-V0	⑥ Color: W=White; B=Black	⑦ Plating code for contacts: T1=Tin-plated	⑧ Plating code: N=Non-plating	⑨ Option code: K0=With pin kink; 01=Nylon 66+GF15%	⑩ Packing code: G=Bag

SPECIFICATIONS

Current Rating: 3A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 10mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstanding Voltage: 800V AC/minute
 Pin Material: Brass

Circuit No.	Dimensions		Circuit No.	Dimensions	
	A	B		A	B
02P	2.50	7.50	09P	20.00	25.00
03P	5.00	10.00	10P	22.50	27.50
04P	7.50	12.50	11P	25.00	30.00
05P	10.00	15.00	12P	27.50	32.50
06P	12.50	17.50	13P	30.00	35.00
07P	15.00	20.00	14P	32.50	37.50
08P	17.50	22.50	15P	35.00	40.00

燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.					
UNIT	SCALE	SHEET	TITLE:		
mm	1 : 1	1 of 1	2.50mm PITCH 180° WAFER		
DRAWN BY	APPROVED BY				
陳錦展	董正一				
2010.12.21	2010.12.21				
GENERAL TOLERANCE					
A1	EN112230532	2012.01.04	陳錦展	X. X±0.25	ANGLE±
A0	NEW RELEASE	2010.12.21	陳錦展	X. XX±0.15	
REV.	DESCRIPTION	DATE	NAME	X. XXX±0.05	
DRAW NO. :			A2502WV-XPNXXXXXXXXX		REV. A1