



SPECIFICATIONS

Current Rating: 15A AC,DC
 Voltage Rating: 600V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 3.5mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstanding Voltage: 5000V AC/minute
 Pin Material: Brass/Tin-plated
 Material: Nylon 66,UL94V-2
 Color: Natural(Translucent)

Ordering Information & Dimensions

PART NO.	Dimensions	
	A	B
C6350WV-02PFV2	6.35	13.97
C6350WV-03PFV2	12.70	20.32
C6350WV-04PFV2	19.05	26.67
C6350WV-05PFV2	25.40	33.02
C6350WV-06PFV2	31.75	39.37
C6350WV-08PFV2	44.45	52.07

		UNIT	SCALE	SHEET	TITLE:
		mm		1 of 1	6.35mm PITCH 180° SINGLE ROW WAFER, FEMALE TYPE
		DRAWN BY	APPROVED BY		
		李勤	董正一		
		2006.02.25	2006.02.25		
		GENERAL TOLERANCE			
A1	REVISE	2007.09.14	X. X±0.25	ANGLE±	DRAW NO.: C6350WV-XPV2
A0	NEW RELEASE	2006.02.25	X. XX±0.15		
REV.	DESCRIPTION	DATE	X. XXX±0.05		
					REV. A1