

## Bi-Material Groove Joint Pliers

- Adjustable-width jaw designed for grasping and turning
- Used for plumbing, automotive and general applications
- Rust-resistant chrome finish
- Machined jaws help grip items securely

Product SKU No.	Type	Length		Box/Ctn
		Inches	mm	
84-034	Groove Joint	8	203	4 / 24
84-024	Groove Joint	10	254	4 / 24



## Bi-Material Pliers Set

- Machined jaws help grip items securely
- Cutting pliers feature induction hardened cutting edges for long life

Product SKU No.	Contains	Box/Ctn
84-056 3 piece set	6" Diagonal 6" Long Nose 6" Slip Joint	4 / 12
84-058 4 piece set	4 Piece Plier Set (84-026, 028, 029, 032) 8" Slip Joint 7" Diagonal 8" Lineman 8" Long Nose	4 / 12
84-079 6 piece set	6 Piece Mini Plier Set (84-018, -119, -122, -124, -125, -126)	0 / 4



## MaxSteel™ Curved Jaw Locking Pliers

- Curved jaws ideal for tightening, clamping, twisting and turning round or faceted objects such as piping or nuts
- Turn screw to adjust holding pressure and fit work
- Non-pinching, pull-style release lever can be actuated with one hand
- Built in wire cutter
- Forged and machined jaws for maximum durability
- Chrome plated to resist corrosion

Product SKU No.	Type	Length		Box/Ctn
		Inches	mm	
84-807	Curved Jaw	5-3/4	145	4 / 24
84-808	Curved Jaw	7-3/8	185	4 / 24
84-809	Curved Jaw	9	225	4 / 24



## MaxSteel™ Straight Jaw Locking Pliers

- Straight jaws ideal for tightening, clamping, twisting and turning flat or faceted objects
- Turn screw to adjust holding pressure and fit work
- Non-pinching, pull-style release lever can be actuated with one hand
- Forged and machined jaws for maximum durability
- Chrome plated to resist corrosion

Product SKU No.	Type	Length		Box/Ctn
		Inches	mm	
84-810	Straight Jaw	7-1/2	190	4 / 24
84-811	Straight Jaw	9	225	4 / 24

