

# MRJE2604 Product Details

[Share](#) | [Print](#) | [Email](#)


Active

## Rotary Switches

MRJE2604

MRJE2604

TE Internal Number: 1825537-2

**Product Highlights** [View All](#)

- 6 Positions
- Angle of Throw = 30.00 °
- Actuator Style = Long Thin Knob
- Code Type = 2 Poles
- Straight Mount Angle

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

**Please Note:**  
Use the Product Drawing for all design activity

Product Type Features	
Angle of Throw (°)	30.00
Actuator Style	Long Thin Knob
Code Type	2 Poles
Mount Angle	Straight
Product Series	MRJE

  

Electrical Characteristics	
Contact Rating	0.4VA

  

Contact Features	
Solder Tail Contact Plating	Gold over Nickel
Contact Base Material	Brass

Housing Features	
Housing Material	Epoxy

  

Configuration Features	
Number of Positions	6

  

Industry Standards	
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
RoHS/ELV Compliance History	Always was RoHS compliant

  

Other	
Brand	Alcoswitch
Comment	Fixed

**Related Products**

Not quite the product you're looking for?  
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Downloaded from [Arrow.com](#)