



NX-ECC203

NX-series EtherCAT Coupler, 2 ports, 125 μ s cycle time, 63 I/O units, max I/O current 10 A, screwless push-in connector, delivered with end cover

Specifications

I/O system	NX I/O Bus
Type of module	Bus coupler
IO-Link master	✘
Suitable for safety functions	✘
SIL according to IEC 61508	None
Communication port(s)	EtherCAT Slave
Number of communication ports	2
Degree of protection (IP)	IP20
Product Height (unpacked)	100 mm
Product Width (unpacked)	46 mm
Product Depth (unpacked)	80 mm
Product Weight (unpacked)	250 g

Accessories



GX-JC03

3-port EtherCAT Junction module, 24 VDC power supply



GX-JC06

6-port EtherCAT Junction module, 24 VDC power supply

GX-JC06-H

6-port EtherCAT Junction module, 24 VDC power supply, with node switches



NX-AUX01

NX-series accessory, DIN rail insulation spacers, set of 3 pcs



NX-AUX02

Terminal block coding pins for 10x NX I/O units (terminal block: 30 pins, unit: 30 pins)



NX-PD1000

NX bus power supply unit, 24 V DC input, non-isolated, screwless push-in connector, 12 mm wide



NX-PF0730

NX I/O power feed unit, 5-24 V DC input, 8 terminals, 10A, screwless push-in connector, 12mm wide



XS6W-6LSZH8SS100CM-Y

Ethernet patch cable, F/UTP, Cat.6A, LSZH (Yellow), 1 m



XS6W-6LSZH8SS200CM-Y

Ethernet patch cable, F/UTP, Cat.6A, LSZH (Yellow), 2 m



XS6W-6LSZH8SS20CM-Y

Ethernet patch cable, F/UTP, Cat.6A, LSZH (Yellow), 0.2 m



XS6W-6LSZH8SS500CM-Y

Ethernet patch cable, F/UTP, Cat.6A, LSZH (Yellow), 5 m



XS6W-6LSZH8SS50CM-Y

Ethernet patch cable, F/UTP, Cat.6A, LSZH (Yellow), 0.5 m