

Model	Voltage VDC	Current AMP	Input WATTS	Fan Speed RPM	AirFlow CFM	Pressure Inch-H2O	Noise dBA
EC9225HH12X	12	0.27	3.24	3000	53.1	0.13	< 35
EC9225H12X	12	0.21	2.52	2600	48.43	0.11	< 31
EC9225M12X	12	0.15	1.8	2200	39.35	0.08	< 25
EC9225L12X	12	0.09	1.08	1800	31.84	0.05	< 22
EC9225LL12X	12	0.07	0.84	1500	27.39	0.04	< 21
EC9225HH24X	24	0.16	4.8	3000	53.1	0.13	< 35
EC9225H24X	24	0.1	2.4	2600	48.43	0.11	< 31
EC9225M24X	24	0.08	1.92	2200	39.35	0.08	< 25
EC9225L24X	24	0.07	1.68	1800	31.84	0.05	< 22

E - EL bearing , B - Two ball bearing , C - One ball One sleeve bearing , S - Sleeve bearing

- Material:impeller&Frame:Plastic(UL 94V-0)
 - Lead Wires:
UL 1007 AWG #28 Or Equivalent
Red Wire Positive(+),Black Wire Negative(-),Yellow Wire Or Blue Wire Signal(FG)
 - Function type is optional.
 - The max air flow and the speed are measured in free air;max air pressure is measured at zero air flow.
 - Noise is measured in anechoic chamber in free air,one meter from intake side.
 - All readings are typical values at rated voltage.
 - Specifications are subject to change without notice.
 - Additional special function may be added according the requirement of customer.
- ※ If any fan requests,please do no hesitate to contact us.