

TITLE	SPEC	TITLE	SPEC
TYPE	TCXO	하증착 MASK	*
MODEL	STD	SPECER(T)	
FREQ	20.000000	주조 MASK	*
MODE	FUND	Burn-In	
Vcc(V)	5.0 ±%	온도검사	
I(mA)	20	REFLOW	
RT(PPM)	±1	MARKING 방식	
TC(PPM)	±5	MARKING 1	TCXO-6TA8
TR(°C)	-10~70	MARKING 2	20.000MHz
R/F(ns)	15/15	MARKING 3	YY.MM
DUTY(%)	45/55	MARKING 4	SUNNY
START-UP(ms)		MARKING 5	
LOAD	2TTL,pF	LEAD	5
OUT-PUT	F01 TTL	포장방식	
E/D		PB-FREE	
JITTER(rms,ps)			
Vc(V)	± V		
PULLING(PPM)	±PPM MIN ±PPM MAX		
SVcc(PPM)	±0.3PPM MAX /±5%		
Sload(PPM)	±0.3PPM MAX /±10%		
T/R(PPM)	±3PPM MIN /±%		
Phase Noise(dBc/Hz)			