

RDC2-0040 BOM

кол-во	позиция	наименование	код товара
2	C1, C2	470 мкФ, 63 В, 13x20	9000247217
4	C3, C4, C18, C19	0.1 мкФ, X7R, 250В 1206	468214461
1	C5	22 мкФ, 100 В, 6.3X11	9000247159
5	C6 - C10	10 мкФ, 10 В, тип А, 10%	868717967
6	C11, C12, C14, C17, C20, C22	0.1мкФ, Y5V 50В, 20%, 0603	226236018
2	C15, C16	0.015мкФ, X7R 50В, 10%, 0603	895412441
1	C21	0.47мкФ, Y5V 50В, -20+80%, 0603	87954344
5	C13, C23 - C26	220пФ, NPO 50В, 5%, 0603	79714346
1	DA1	TDA8950TH/N1,118	9000275879
4	R1 - R4	0.063Вт 0603 10 кОм, 5%	65097
1	R5	0.063Вт 0603 470 Ом, 5%	56821
1	R6	не устанавливать	
1	R7	0.125Вт 0805 30 кОм, 5%	364055299
2	R11, R12, R10	0.063Вт 0603 10 Ом, 5%	61172
2	VT1, VT2	BSS138	9000476837
1		Печатная плата RDC2-0036	9000488861