



Specification

1. Operating Voltage Range6--15VDC
2. Rated Voltage 12 VDC
3. Max Rated Current90 mA
4. Min Sound Output 95±2 dB at100cm
5. Freuency..... 1500~4000 Hz
6. Tone Nature.....Siren
7. Operating Temperature range-20 ~ +60°C
8. Store Temperature-30~+70°C
9. Housing Material.....ABS
10. Weight45g

No.		DESCRIPTION		APPROVED	DATE	KEPO NINGBO KEPIE IMPROVING ELECTRONIC CO.,LTD http://www.chinaacoustic.com
DATE OVERHAULED		APPROVALS		DATE	UNIT	
DRAWN		CHECKED		APPROVED	SCALE	DWG NO.
XX #		90° FORMED ±2°		03.08.04	NOT TO SCALE	KEP3.840.456
FIRST ANGLE PROJECTION		APPROVED				SHEET
						VER 1.0