



Specifications			Notes	Revision History					
Description	Value	Unit		Version	Description			Date	Approved
Technology	Electro-Mechanical		1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS	1	Released from Engineering			10/21/2013	J.S
Resonant Frequency	2,400	(Hz)							
Rated Voltage	5	(V)							
SPL @ 10cm	87	(dBA)							
Coil Resistance	47	(ohm)							
Mount Type	Surface Mount								
Voltage Range	3 ~ 8	(V)							
Max Rated Current	40	(mA)							
Housing Material	PPS								
Operating Temperature	-30 ~ +70	°C							
Storage Temperature	-30 ~ +70	°C							
Weight	2	(g)							
				Electro-Mechanical Transducer			TE122005-1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[TE062603-1](#) [TE122005-1](#) [TE122206-1](#) [TE092703-3](#) [TE142003-1](#) [TE062701-1](#)