


Ferrite Shallow Pot datasheet

Threaded hole

- High resistance to demagnetisation
- Custom designs available
- Max. operating temperature 120°C.
- Mild steel pot
- Zinc plated
- Female thread



Product Information

Product No.	Diameter	Pot height	Total height	Thread size	Weight	Pull force
		mm			kg	
E863	20	6	13	M3	0.011	3.0
E864	25	7	15	M4	0.022	4.0
E865	32	7	15	M4	0.032	8.0
E866	36	8	16	M4	0.045	10.0
E867	40	8	18	M5	0.060	12.5
E868	47	9	17	M4	0.090	18.0
E869	50	10	22	M6	0.110	22.0
E870	57	10.5	18.5	M4	0.145	28.0
E871	63	14	30	M8	0.240	35.0
E872	80	18	34	M10	0.520	60.0