

FEATURES

- IP44 rated
- Voltage ratings of 20 to 25V offered in this range
- Straight body orientation
- All models offered in the range are highly reliable and excellent quality
- Maximum operating temperature of 40 °C

RS PRO IP44 Purple Cable Mount 2P Industrial Power Plug, Rated At 16.0A, 20 → 25V

RS Stock No.: 668-5357



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted brand RS PRO, comes a range of high-quality wall mountable power connectors. Manufactured to industry standards these connectors are easy to assemble and are a fantastic industrial plug solution for powering tools and machinery at a range of different voltage requirements.

General Specifications

Syntetical Description	Plug
Pole Format	2P
Gender	Male
Body Orientation	Straight
Material	Engineering Plastic
Colour	Purple
Applications	Providing power for machinery on construction sites, Woodworking machines, Maintenance workshops in the light industry

Electrical Specifications

Type of Current	AC
Current Rating	16A
Voltage Rating	20V to 25V
Working Frequency	50Hz
Plug/Socket	Plug
Low voltage	Yes

Mechanical Specifications

Mounting Type	Cable Mount
----------------------	-------------

Operation Environment Specifications

Maximum Operating Temperature	40°C
Minimum Operating Temperature	-25°C

Protection Category

IP Rating	IP44
-----------	------

Approvals

Compliance/Certifications	EN61340
---------------------------	---------

