



Number of contacts

4+

40 A 400/690 V 6 kV 3
 + 2 additional signal contacts
 10 A 250 V 4 kV 3



Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
Han® Q , Axial screw termination, Contact surface: Silver plated  With Han-Quick Lock® signal contacts	2,5 ... 6 4 ... 10	09 12 006 2662 09 12 006 2663	09 12 006 2762 09 12 006 2763	 Stripping length Power contacts 8 mm Stripping length Signal contacts 10 mm Tightening torque 1.8 Nm
Han® Q , Axial screw termination, Contact surface: Silver plated Without signal contacts	2,5 ... 6 4 ... 10	09 12 006 2665 09 12 006 2666	09 12 006 2765 09 12 006 2766	

Han Q