

HUBER+SUHNER® DATA SHEET

Within Series Adaptor: 32_MMBX-50-0-5/111_N

Rev.: G 

Description

Adaptor plug/plug
MMBX plug (male) / MMBX plug (male)
Slide - snap interface
Interface standard
Series MMBX - SUHNER-MMBX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 12.4 GHz

Mechanical Data

Number of matings 100
Weight 0.0005 kg

Environmental Data

Operating Temperature -55 °C to 155 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts

Interface - MMBX plug (male)

	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE	

Interface - MMBX plug (male)

	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00013890

Ordering Information

Tray package 32_MMBX-50-0-5/111_NY
Single package 32_MMBX-50-0-5/111_NE

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions