

56924

Bucket, 470 mm, , Red



An ideal “mixing station”, where you can mix ingredients stored in smaller Vikan buckets or in 20 Litre Buckets. Perfect for solid or liquid ingredients. Large enough to meet all your mixing needs, but small enough for safe lifting and transport. Features like the bottom handle and a rounded rim and lip also facilitate ergonomic, no-spill lifting and pouring. Durable bevelled measurements inside.

Technical Data

Item Number	56924
Volume	20 Litre(s)
Material	Polypropylene Stainless Steel
Suitable for Food Contact (EU 1935/2004), DoC ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	5 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	40 Pcs
Quantity Per Layer (Pallet)	10 Pcs.
Box Length	800 mm
Box Width	455 mm
Box Height	415 mm
Length	470 mm
Width	470 mm
Height	380 mm
Gross Weight	1,97 kg
Net Weight	1,76 kg
Cubik metre	0,0805 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	100 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature	-20 °C
Max. drying temperature	120 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Gtin-13 Number	5705020569241
GTIN-14 Number (Box quantity)	15705020569248
Commodity Code	39233090
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care

units, before use.

1. See Declaration of Compliance for further details on food contact