


coupling socket NPHS-D6-P-G12

Part number: 8059269

★ Core product range

FESTO



Data sheet

Feature	Value
Nominal size	11 mm
Operating pressure complete temperature range	-0.95 ... 10 bar
Standard nominal flow rate	1,950 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-10 ... 60 °C
Nominal tightening torque	14 Nm
Tolerance for nominal tightening torque	± 20 %
Product weight	113 g
Pneumatic connection, port 1	Male thread G1/2
Materials note	Conforms to RoHS