

SEK CAB FLAT SH RND AWG28/7 20P 30,48m



Part number	09 18 020 7007
Specification	SEK CAB FLAT SH RND AWG28/7 20P 30,48m
HARTING eCatalogue	https://b2b.harting.com/09180207007

Image is for illustration purposes only. Please refer to product description.

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)

Version

Cable length	30.48 m
Shielding	Shielded
Number of cores	20
Core structure	AWG 28/7

Technical characteristics

Impedance	100 Ω
Limiting temperature	-30 +75 °C unmoved -20 +75 °C moved
Conductor resistance @ 20 °C	≤216 Ω/km

Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	е



Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	UL 1581 Sec. 1061 UL PLCC, CL2
CE	Yes

Commercial data

Packaging size	1
Net weight	0.01 g
Country of origin	USA
European customs tariff number	85444993
eCl@ss	27061801 Data and communication cable (copper)