








Number of contacts

# 8



Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		
Module  	<b>09 14 001 3011</b>	<b>09 14 001 3111</b>	M   F 	

Han Modular

Identification	Wire gauge (mm <sup>2</sup> )	Part number		Drawing	Dimensions in mm												
		Male contact	Female contact														
Han® GigaBit insert 8 + shielding Order crimp contacts separately  		<b>09 14 008 3011</b>	<b>09 14 008 3111</b>	M   F 													
D-Sub crimp contacts				<table border="1"> <thead> <tr> <th colspan="2">Wire gauge</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0,08-0,21 mm<sup>2</sup></td> <td>AWG 28-24</td> <td>4 mm</td> </tr> <tr> <td>0,13-0,33 mm<sup>2</sup></td> <td>AWG 26-22</td> <td>4 mm</td> </tr> <tr> <td>0,21-0,52 mm<sup>2</sup></td> <td>AWG 24-20</td> <td>4 mm</td> </tr> </tbody> </table>	Wire gauge		Stripping length	0,08-0,21 mm <sup>2</sup>	AWG 28-24	4 mm	0,13-0,33 mm <sup>2</sup>	AWG 26-22	4 mm	0,21-0,52 mm <sup>2</sup>	AWG 24-20	4 mm	
Wire gauge		Stripping length															
0,08-0,21 mm <sup>2</sup>	AWG 28-24	4 mm															
0,13-0,33 mm <sup>2</sup>	AWG 26-22	4 mm															
0,21-0,52 mm <sup>2</sup>	AWG 24-20	4 mm															
	0,08-0,21	09 67 000 7576	09 67 000 7476														
	0,13-0,33	<b>09 67 000 5576</b>	<b>09 67 000 5476</b>														
	0,21-0,52	<b>09 67 000 8576</b>	<b>09 67 000 8476</b>														

Stock items in bold type