

# Product data sheet

Specifications



## Easy PDU, Metered, Zero U, 32A, 230V, (20)C13 & (4)C19 ; IEC309

EPDU1132M

### Overview

Lead time Usually in Stock

### General

Provided equipment Installation guide  
Toolless mounting kit  
User manual  
Vertical mounting brackets

### Physical

Cable length 3.00 m  
Colour Black  
Depth 4.44 cm  
Height 117.5 cm  
Net weight 3.72 kg  
Width 6.2 cm

### Input

Permissible voltage 220...240 V  
Max line current 32 A  
Input current limits 32 A  
Load capacity 7360 VA  
Network frequency 50/60 Hz  
Plug standard IEC 60309 32 A 2P + E  
Input voltage 200 V  
208 V  
230 V

### Output

Number of power socket outlets 20 IEC 60320 C13  
4 IEC 60320 C19

### Conformance

Product certifications CE  
TUV  
EAC

## Environmental

Ambient air temperature for operation	-5...45 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

## Packing Units

Package 1 Weight	4.48 kg
Package 1 Height	132 cm
Package 1 width	16 cm
Package 1 Length	11 cm

## Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------