

Ultrasonic Rings

PZT4-Model型号	电容量Capacity CT (pF)	Loss损耗	Radial Frequency 谐振频率	Coupling Modulus 耦合系数	Quality Factor品质 因数
		tgo (%)	Fs (kHz)	Kp (%)	Qm
φ 10* φ 5*2	377	0, 37	143, 1	0, 58	≥1000
φ 25* φ 9. 5*3	1554	0, 38	61, 57	0, 58	≥1000
φ 25* φ 9. 5*5	984	0, 41	62, 19	0, 58	≥1000
φ 40* φ 15*5	2893	0, 39	38, 9	0, 58	≥1000
φ 38* φ 15*5	2400	0, 41	39, 5	0, 58	≥1000
φ 35* φ 15*5	1900	0, 4	42	0, 58	≥1000
φ 45* φ 15*5	3750	0, 41	38	0, 58	≥1000
φ 50* φ 17*5	4141	0, 42	32, 2	0, 58	≥1000
φ 65* φ 30*10	3343	0, 41	22, 2	0, 58	≥1000
φ 50*2. 6	8222, 5	0, 4	43, 43	0, 58	≥1000
φ 50*2. 48	8303	0, 4	43, 58	0, 58	≥1000
PZT8-Model	Capacity CT (pF)	Loss	Radial Frequency	Coupling Modulus	Quality Factor
		tgo (%)	Fs (kHz)	Kp (%)	Qm
φ 10* φ 5*2	318	0, 29	152	0, 53	800
φ 15* φ 6. 5*2	671	0, 29	107	0, 53	800
φ 40* φ 12*5	2044	0, 28	46, 8	0, 53	800
φ 50* φ 17*5	3176	0, 29	35, 25	0, 53	800
φ 50* φ 23*6. 5	2194	0, 27	31, 5	0, 53	800
Ultrasonic Discs					