
Item no.: 282-687
Product description: 3-CONDUCTOR GROUND TERMINAL BLOCK



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.2 - 6 mm ²
Cross section [AWG]	24 - 10 AWG
Connection method	CAGE CLAMP® CONNECTION
Weight	27.874 g
Color	green-yellow
Wiring type	Front-entry
No. of connection Points	3
No. of potentials	1
Height	32.5 mm
Height	1.28 in
Width	8 mm
Width	0.315 in
Depth	93 mm
Depth	3.66 in
Strip length from	12 mm
Strip length to	13 mm
Strip length	0.49 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
282-687	ABS	05-HG476175/3-PDA			6,0
282-687	BV	07436/Co	800	41	6,0
282-687	CCA	NL5448			6
282-687	CSA	154112-1505033			24-10
282-687	DNV	E-10423	800	41	6,0
282-687	GL	17295-00HH			6
282-687	KEMA	2036290.01			6
282-687	KR	HMB05880-EL001	500/800	10/46	6
282-687	LR	91/20112(E6)	800	41	6,0
282-687	PRS	TE/1718/880590/08			6
282-687	RMR	11130002	800	41	6,0
282-687	UR	E45172			24-10

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected