


**SPECIFICATIONS**

Voltage rating: 100V AC, DC  
 Current rating: 1A, AC, DC (AWG#26)  
 Withstanding Voltage: 500V AC/minute  
 Insulation resistance: 500M Ω min  
 Temperature range: -25℃ - +85℃  
 Contact resistance: 20mΩ max

**HOUSING**

Part No: SCT1501H-XXP  
 Poles: 02-16  
 Material: Nylon 66, UL94V-0  
 Q' TY: 1000 pcs/bag

PART NO	DIMENSION	
	A	B
SCT1501H-02	1.50	4.50
SCT1501H-03	3.00	6.00
SCT1501H-04	4.50	7.50
SCT1501H-05	6.00	9.00
SCT1501H-06	7.50	10.50
SCT1501H-07	9.00	12.00
SCT1501H-08	10.50	13.50
SCT1501H-09	12.00	15.00
SCT1501H-10	13.50	16.50
SCT1501H-11	15.00	18.00
SCT1501H-12	16.50	19.50
SCT1501H-13	18.00	21.00
SCT1501H-14	19.50	22.50
SCT1501H-15	21.00	24.00
SCT1501H-16	22.50	25.50

					OPERATION	DRAW	Judy.Huang	2006/05/02	SCALE		 <b>森康达电子有限公司</b> SCONDAR ELECTRONIC LIMITED		
					~ 10	±0.15			UNIT	mm			
					20 ~ 30	±0.30	DESIGN		SIZE	A4	PART NO.	SCT1501H-XXP	
0	05/12/27				30 ~	±0.50	CHECK	Micky.Liu	2006/05/02	SHEET	1/1	TITLE:	ZH1.5 HOUSING
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	APPROVE	Angle	± 2'	APPROVE	Hellen.Li	2006/05/02	PROJ.	◆	DRAWING NO.	SCT1501
					DIM	TOL							