

1 2 3 4 5 6 7 8 9 10

A

B

C



D

E

F

G

H



SPECIFICATIONS

Voltage Rating: 250V AC/DC

Current Rating: 3A AC/DC

Withstanding Voltage: 800V AC/minute

Insulation Resistance: 1000MΩ min.

Temperature Range: -25° C - +85° C



Contact Resistance: 20mΩ max

HOUSING



Part No: SCT2511H-XXP

Poles: 2-15

Material: Nylon 66, UL94V-0



PART NO.	Dimensions	
	A	B
SCT2511H-02P	2.50	7.00
SCT2511H-03P	5.00	9.50
SCT2511H-04P	7.50	12.00
SCT2511H-05P	10.00	14.50
SCT2511H-06P	12.50	17.00
SCT2511H-07P	15.00	19.50
SCT2511H-08P	17.50	22.00
SCT2511H-09P	20.00	24.50
SCT2511H-10P	22.50	27.00
SCT2511H-11P	25.00	29.50
SCT2511H-12P	27.50	32.00
SCT2511H-13P	30.00	34.50
SCT2511H-14P	32.50	37.00
SCT2511H-15P	35.00	39.50

					OPERATION	DRAW	CHENA	05/12/27	SCALE		 森康达电子有限公司 SCONDAR ELECTRONIC LIMITED	
					~ 10 ±0.15	DESIGN			UNIT	mm		
					20 ~ 30 ±0.30	CHECK	MICKY	05/12/27	SIZE	A4	PART NO.	SCT2511H-XXP
					30 ~ ±0.50	APPROVE	HELLEN	05/12/27	SHEET	1/1	TITLE:	EH2.5 Housing
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	APPROVE	Angle DIM	± 2° TOL			PROJ.		DRAWING NO.	SCT2511

1 2 3 4 5 6 7 8 9 10