

Cat5e 350 MHz Molded (UTP) Ethernet Cable (RJ45 M/M) - Blue, 20 ft. (6.09 m)

MODEL NUMBER: N002-020-BL



Description

Tripp Lite's 20-ft. (6.09 m) Blue category 5e (Cat5e) patch cable has 2 standard RJ45 molded male connectors featuring integral strain relief. The cable is manufactured from PVC 4-pair stranded UTP and is rated for 350MHz/1Gbps communication. All cables are offered in a variety of lengths and colors for all category 5 (Cat5) and 5e cabling needs. Snagless category 5e patch cables are also available.

Features

- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 20-ft. (6.09 m) Color: Blue Connectors: RJ45 male
- Feature molded connectors with integral strain relief
- PVC 4-pair stranded UTP
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- Available in other colors and lengths
- Also available in a snagless design (N001 series) to protect the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- Also available - Cat6 cables (N201 series)

Highlights

- Premium cabling for Category 5 and 5e applications—rated for 350 MHz/1 Gbps communications
- IEEE 802.3ab
- PVC 4-pair stranded UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors

System Requirements

- For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications

Package Includes

- 20-ft. (6.09 m) Cat5e Blue Patch Cable Molded 350MHz

Specifications

OVERVIEW	
UPC Code	037332172808
Technology	Cat5/5e



POWER	
Power Over Cable (PoC) Support	No
PHYSICAL	
Color	Blue
Cable Jacket Material	PVC
Cable Jacket Rating	CM
Cable Shielding	UTP
Cable Outer Diameter (OD)	5.0mm
Number of Conductors	4 Pair
Conductor Material	Stranded Copper
Conductor Gauge	26 AWG
Cable Length (ft.)	20
Cable Length (m)	6.10
Cable Length (in.)	240
Cable Length (cm)	609.6
Shipping Dimensions (hwd / cm)	25.40 x 20.32 x 1.27
Shipping Dimensions (hwd / in.)	10.00 x 8.00 x 0.50
Shipping Weight (kg)	0.18
Shipping Weight (lbs.)	0.40
COMMUNICATIONS	
Bandwidth per TIA Standard	100 MHz
Maximum Bandwidth as Tested	350 MHz
Network Compatibility	1 Gbps (Gigabit)
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Crossover Wiring	No
Contact Plating	Gold
Connector Type	Molded
Wiring Configuration	EIA/TIA 568B
FEATURES & SPECIFICATIONS	
IP68 Rated	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Snagless Connector	No
Antibacterial	No
STANDARDS & COMPLIANCE	
Certifications	RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>