



Features and Benefits

Molex PowerCat 5E U/UTP Patch Cards are key components of PowerCat 5E U/UTP End-to-End Solution and are designed to support data networks for 10/100BASE-T and 1000BASE-T applications.

The patch cable is made from high quality four pair 24 AWG stranded copper wire. Available in a range of colors and lengths, PowerCat 5E patch cords are preterminated with RJ45 plugs and feature anti-snag slim strain relief slip on boots.

- 4 pair 24 AWG stranded wire
- Pre-terminated with WE8W plugs
- Slim clear anti-snag slip on boots
- Suitable for EIA 568A or 568B wiring applications
- LSOH sheath
- RoHS Compliant

Commercial Standards

ISO/IEC 11801:2002/Amd 2:2010 Cat 5, TIA-568-C.2 Cat 5E

Pending Approvals:
UL-1863, CSA C2.2

Fire Propagation Tests:

LSOH Sheath: CSA FT1, IEC 60332-1, IEC 61034

Technical Information

Mechanical Characteristics - Cable

Conductor size: 24 AWG stranded copper wire
 Nom. O.D.: 5.4mm
 Sheath: LSOH
 Bend radius: 4X O.D.
 Operating temperature range: -20°C to 60°C

Mechanical Characteristics - Plug

MIN operating life: 750 insertion cycles
 RJ45 plug and boot material: Clear polycarbonate
 Contact material: 0.35mm thick copper alloy
 Contact plating: Selective gold
 RJ45 plug dimensions compliant with: ISO/IEC 60603-7-4 and FCC 47 Part 68

Electrical Characteristics

Max voltage: 150 VAC (max)
 Max current: 1.5A @ 25°C

ORDERING INFORMATION

Order No.	SAP No.	Description
PCD-01000-**	Consult Molex	PowerCat 5E U/UTP Patch Cord LSOH 0.5m
PCD-01001-**	Consult Molex	PowerCat 5E U/UTP Patch Cord LSOH 1m
PCD-01002-**	Consult Molex	PowerCat 5E U/UTP Patch Cord LSOH 1.5m
PCD-01003-**	Consult Molex	PowerCat 5E U/UTP Patch Cord LSOH 2m
PCD-01005-**	Consult Molex	PowerCat 5E U/UTP Patch Cord LSOH 3m
PCD-01009-**	Consult Molex	PowerCat 5E U/UTP Patch Cord LSOH 5m
PCD-01013-**	Consult Molex	PowerCat 5E U/UTP Patch Cord LSOH 7m
PCD-01019-**	Consult Molex	PowerCat 5E U/UTP Patch Cord LSOH 10m

Insert color code in place of ** in part number when ordering Patch Cords:
 OC=Red, OE=Grey, OH=Blue, OJ=Green, OK=Yellow, OW=White, OP=Purple, ON=Orange, BK=Black

MOLEX PREMISE NETWORKS

Americas
 Tel: 630 969 4550
 www.molexpn.com

EMEA
 Tel: 44 (0) 2392 205800
 www.molexpn.co.uk

APAC
 Tel: 61 3 9971 7111
 www.molexpn.com.au