


flow control valve
GRO-1/8-B
 Part number: 151216



Data sheet

Feature	Value
Valve function	Throttle function
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	G1/8
Adjusting element	Knurled screw
Mounting type	Optional Front panel installation with through hole
Standard nominal flow rate in flow control direction	210 l/min
Operating pressure	0 ... 10 bar
Ambient temperature	-20 ... 60 °C
Material housing	Wrought Aluminium alloy
Nominal size	3 mm
Assembly position	Any
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Medium temperature	-20 ... 60 °C
Product weight	31 g
Materials note	Conforms to RoHS
Material seals	NBR
Material adjusting screw	High alloy steel
Material nut	Wrought Aluminium alloy
Material sleeve	POM