



Cable gland, Thread type: metric, Material: PA 6.6, Protection: IP 66, Colour: Black

RAL: 9005

Business data

Abez 3 - product description	Cable gland
Packaging unit	10
Quantity unit	PC
Weight per piece (not including packaging)	14.7
Weight per piece (including packaging)	15.1
Unit of weight	G
Customs number	39269097
Country of origin	DE

Datasheet

RS Stock No.1856101



Technical Data

Dimensions

Length	40 mm
Width	40 mm
Height	38.7 mm
Installation height	23.7 mm
Diameter of screw head	40 mm

Thread

Thread type	Metric
Thread size	20 mm
Thread pitch	1.5 mm
Thread length (L)	15 mm

Datasheet

RS Stock No.1856101



Technical Data

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	120 °C
Sealing material	TPE
Type of seal	Seal ring
Halogen-free	✓
Silicone-free	✓

Further technical data

Mounting type	Screws
Protection	IP66
Spanner width (AF)	38 mm
With counter nut	✓
Strain relief	✓
Hexagonal corner size	40 mm
Torque for the locknut	3 Nm

Datasheet

RS Stock No.1856101



Media

