


DMS-20PC-1-DCM-C

In Production

Recommended

RoHS

Appearance & Shape



METER DEPTH: 1.00 in. (25.4mm)

Features

3.5 Digit, Self-Powered Standard Red LED Digital DC Voltage Monitor: +8.0 to +50.0Vdc Input

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

DMS-20PC-1-DCM-C



Specifications

Productseries	DMS-20PC-0/1/2/8-DCM
Product Series Features	DMS-20PC-0/1/2/8-DCM
Measuring Range(DCV)	8V to 50V
Display Type	LED
Color	Red
Number of Digits	3
Digit Height (mm)	9.4mm
Power Supply Type	2-Wire Self Powered
Power Supply(DCV)	8V to 50V
DC Power Supply Current (mA)Max	13mA
Self Powered	Yes
Operatingtemperature(degC)	-25°C to 60°C
Humidity	0% to 95%
Measurment Type	DC Volts
Mounting Type	Panel Mount
Accuracy	+/-0.1V
Case Material	Polycarbonate
Configurable DPM	No
Daylight Readable	No
Digit Height (inch)	0.37inch
Resolution (V)	0.01V
Update Rate (samples /sec)	2.5
Weight (g)	28g
Weight (oz)	1 $\frac{3}{8}$

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.