



fitted with

- work equipment**
- connected load**
- power consumption**
- luminous flux**
- luminous efficacy**
- light distribution**
- light colour**
- color rendering index (CRI)**
- system of protection**
- class of protection**
- technology**
- usage**
- luminaire body**
- lamp cover**
- weight (net)**
- mains supply**

- design**
- fastening**
- dimension**
- special features**


- LED
- Energy efficiency category A+
- without
- 18-30 V; DC
- approx. 12 W
- approx. 900 lm
- approx. 75 lm/W
- direct
- neutral white, approx. 5000 K
- > 80
- IP 67
- III
- switchable
- external
- aluminium, anodised, aluminium coloured anodised
- screen, clear
- approx. 1.2 kg
- built-in plug
- Serie_763
- mounted version
- L-angle, clamp
- A=370 mm
- Power equipment



Serie_763

illuminance

distance: 100 cm
Em: 340 lx
Emax: 443 lx
Emin: 212 lx



luminous intensity

