Hirschmann Automation and Control GmbH






MICRO-SMD CLIP 1

Industrial Connectors:Measuring and Testing Equipment:Alligator clips:0.64 mm system

Description	Spring-loaded, two-pole test clip, specially designed for SMD components. Gold- plated, hardened tip for testing circuits, flat-nosedgrips for individual components; notch for gripping thin wires. Balanced spring force permits testing of large and small components; 0.64 mm pin connection; electrically insulated spring.
Type	MICRO-SMD CLIP 1
Order No.	972 416-100
System	0,64 mm system
Clamping range	0 mm to 8 mm
Housing Color	black
Drawing	Moon



Technical data		
Type of contact	pin	
Type of termination	2 x0,64 mm diameter pin	
Rated voltage	DC 60 V	
Contact resistance	6 mOhm	
Material		
Contact material	copper beryllium	
Contact surface material	gold-plated	
Housing material	PBT	
Environmental conditions		
Temperature range	-30 °C to +100 °C	
Inflammability class		
Housing	94 HB	