



## Specifications

- Current rating:1A AC,DC
- Voltage rating:30V AC,DC
- Temperature range:-40°C~+105°C
- Contact resistance:30mΩMax.
- Insulation resistance:100MΩMin.
- Withstanding voltage:200V AC/minute
- \*Compliant with RoHS and REACH\*
- \*Meet the HF/Halogen Free,need to customize\*
- \*Contact CJT for details\*

Standards

## Assembly layout







# A0801 SERIES



0.80mm pitch wire to board connector

## A0801H-XP-2

0.80mm pitch Housing


### Reference Informations:

- \*Material:LCP,UL94V-0
- \*Suitable CJT A0801-T series Terminal
- \*Mates with CJT D0801WV-S,WR-S-XP series Wafer
- \*Color:Natural



Ordering Information:  
A0801H-XP-2 - \*\*\*  
1 2

- 1.Part No.
- 2.Material:  
(Blank):LCP,UL94V-0  
GWT:LCP,UL94V-0,GWT 750°C



PART NO.	Dimensions	
	A	B
2P	0.80	2.40
3P	1.60	3.20
4P	2.40	4.00
5P	3.20	4.80
6P	4.00	5.60
7P	4.80	6.40
8P	5.60	7.20
9P	6.40	8.00
10P	7.20	8.80
11P	8.00	9.60
12P	8.80	10.40
13P	9.60	11.20
14P	10.40	12.00
15P	11.20	12.80
16P	12.00	13.60
17P	12.80	14.40
18P	13.60	15.20
19P	14.40	16.00
20P	15.20	16.80