

PVC Cable Guard for rewirable connectors



Description

- 1 Function:
- Press-Fit Version
- bend protection for cable

Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [CAD-Drawings](#), [Accessories](#), [Detailed request for product](#)

All Variants

Suitable for	Color	For cables with outer diameter of	Length [mm]	Order Number
1651, 4013, 4020, 4021, 4022, 8101, 8111, 9013	white	8.7 mm	39.4 mm	4311.0053
0104, 0104U, 0106	white	10 mm	39 mm	4311.0063
0104, 0104U, 0106	white	8 mm	38 mm	4311.0064
4012	white	8 mm	37.5 mm	4311.0067
1651, 4013, 4020, 4021, 4022, 8101, 8111, 9013	white	10 mm	39 mm	4311.0068
0104, 0104U, 0106	black	8 - 10 mm	40.3 mm	4311.9301
0104, 0104U, 0106	grey	8 - 10 mm	40.3 mm	4311.9302
1651, 4013, 4020, 4021, 4022, 8101, 8111, 9013	black	8.7 - 10 mm	40.3 mm	4311.9305
1651, 4013, 4020, 4021, 4022, 8101, 8111, 9013	grey	8.7 - 10 mm	40.3 mm	4311.9306
4012	black	8 - 10 mm	36.7 mm	4311.9307
1251	black	6.5 mm	30 mm	4311.9309
0101, 0102, 0104, 0104U, 0106, 0112, 4771, 4772	black	8 mm	38 mm	4311.9310
0101, 0102, 0112, 4771, 4772	black	10 mm	40 mm	4311.9313
0104, 0104U, 0106	grey	10 mm	39 mm	4311.9315
1651, 4013, 4020, 4021, 4022, 8101, 8111, 9013	black	8.7 mm	39.4 mm	4311.9316
1651, 4013, 4020, 4021, 4022, 8101, 8111, 9013	grey	8.7 mm	39.4 mm	4311.9317
1651, 4013, 4020, 4021, 4022, 8101, 8111, 9013	black	10 mm	39 mm	4311.9318
1651, 4013, 4020, 4021, 4022, 8101, 8111, 9013	grey	10 mm	39 mm	4311.9319
4012	black	8 mm	37.5 mm	4311.9320
4012	grey	8 mm	37.5 mm	4311.9321
4012	black	10 mm	37 mm	4311.9322
1251	white	6.5 mm	30 mm	4311.9324

Packaging unit 100 Pcs