

NCG-M122B



Products → Low Voltage Products and Systems → Installation Products
→ Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

General Information

Extended Product Type:	NCG-M122B
Product ID:	7TCA303070R0035
EAN:	5415022423570
Catalog Description:	NYLON CG M12X1.5 3.0-6.5MM BLK
Long Description:	Non Armoured Cable Gland, Thread Size M12, Cable Range 3 to 6.5 Millimeters, Thread Length 8 Millimeters, Nylon, Black

Ordering

EAN:	5415022423570
Minimum Order Quantity:	10 piece
Customs Tariff Number:	3917400090

Dimensions

Product Net Weight:	4.536 g
----------------------------	---------

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	89.916 mm
Package Level 1 Height:	89.916 mm
Package Level 1 Depth / Length:	180.086 mm
Package Level 2 Units:	100 piece
Package Level 2 Width:	400.05 mm
Package Level 2 Height:	279.908 mm
Package Level 2 Depth / Length:	100.076 mm

Additional Information

Brand / Label:	T&B
Color:	Black
Function:	General purpose, Panel building, Light fixture and housings
Material:	Nylon
Product Main Type:	CABLE GLANDS AND ACCESSORIES
Product Name:	Nylon Cable Gland
Product Type:	Non Armoured Cable Gland
Standards:	UL514B, CSA, RoHS, WEEE, LVD

UPC:

786210151694

Certificates and Declarations (Document Number)

Data Sheet, Technical Information: TDS000030

Instructions and Manuals: NCG-M122B

Classifications

ETIM 6: EC000441 - Cable screw gland

UNSPSC: 39121431

