



Technical characteristics

Degree of protection acc. to IEC IP68
60529

Technical characteristics

Material (cable glands) Metal

Identification	Size	Clamping range (mm)	Part number	Drawing (dimensions in mm)
----------------	------	---------------------	-------------	----------------------------

Cable gland,
EMC version

M20	4 ... 6,5
M20	6,5 ... 9,5
M20	7 ... 10,5
M20	9 ... 13
M25	6,5 ... 9,5
M25	9 ... 13
M32	11,5 ... 15,5
M32	14 ... 18
M40	17 ... 20,5
M40	20 ... 25

19 62 000 5081
19 62 000 5080
19 62 000 5082
19 62 000 5084
19 62 000 5090
19 62 000 5092
19 62 000 5094
19 62 000 5096
19 62 000 5097
19 62 000 5098

cablе-Ø D	SW	E	shield-Ø B
6.5 ... 9.5	22	24.4	3.5 ... 8.5
4 ... 6.5	22	24.4	2.5 ... 6.5
7 ... 10.5	22	24.4	6.5 ... 10.5
9 ... 13	22	24.4	6.5 ... 10.5
6.5 ... 9.5	22	31.2	3 ... 8
9 ... 13	28	31.2	4.8 ... 8
11.5 ... 15.5	35	38.5	8 ... 13.5
14 ... 18	35	38.5	9 ... 14.5
17 ... 20.5	43	47.3	15 ... 20
20 ... 25	43	47.3	15 ... 20

