


**POS sockets in 7,62mm/.300" DIP spacing are either supplied with or without bars in the centre depending on plastic wafer availability. If you need sockets without centre bars, then please always order with POO instead of POS.**

Pin	Dimension		Available Pinouts of Series		
	"A"	"B"	POS	POO	PCL
10	12,60	5,08 .200"	-	-	<b>-210-</b>
6	7,60	7,62 .300"	<b>-306-</b>	-	-
8	10,10		<b>-308-</b>	-	-
10	12,60		<b>-310-</b>	-	-
14	17,70		<b>-314-</b>	<b>-314-</b>	<b>-314-</b>
16	20,30		<b>-316-</b>	<b>-316-</b>	<b>-316-</b>
18	22,80	7,62 .300"	<b>-318-</b>	<b>-318-</b>	<b>-318-</b>
20	25,30		<b>-320-</b>	<b>-320-</b>	<b>-320-</b>
22	27,80		on request	on request	-
24	30,40		<b>-324-</b>	<b>-324-</b>	-
28	35,50		<b>-328-</b>	<b>-328-</b>	-
16	20,32		10,16 .400"	on request	on request
22	27,80	on request		on request	on request
24	30,60	on request		on request	on request
24	30,50	15,24 .600"	<b>-624-</b>	<b>-624-</b>	on request
28	35,50		<b>-628-</b>	<b>-628-</b>	<b>-628-</b>
32	40,60		<b>-632-</b>	<b>-632-</b>	<b>-632-</b>
36	45,70		<b>-636-</b>	on request	-
40	50,80		<b>-640-</b>	<b>-640-</b>	<b>-640-</b>
48	60,96		<b>-648-</b>	on request	on request
64	81,26	22,86 .900"	on request	-	-



**Specifications**  
PBT and high temp plastic depending on type.  
See page 64 of this catalogue and contact factory for more details.

**Insulator body**  
POS series = open insulator - see drawings above  
POO series = open insulator w/o centre bars  
PCL series = closed insulator body

**Terminals**  
The POS, POO and PCL series are available with many different terminal styles. The most common terminal styles are shown on the right hand side of this page. Many other additional terminals can be found at the end of this catalogue. Custom design terminals are available on request.

