

15

1532 02

Jack connectors






Jack plug according to JEITA RC-5325A JC35P4, 3.5 mm, 4 poles/stereo, straight version, with bend protection and solder terminals

State: Active

15

1532 02



Environmental conditions

Temperature range -20 °C/+70 °C

Materials

Insulating body	PBT GF
Contact	CuZn/steel, nickel-plated
Insulation	POM
Housing	PE

Connectable conductors for solder area

Cable diameter 4 mm

Electrical data (at T_{amb} 20 °C)

Contact resistance	≤ 50 mΩ
Rated current	1 A
Rated voltage	34 V AC/DC
Rated impulse voltage	500 V/60 s
Insulation resistance	≥ 100 MΩ

Associated products

Counterparts		
☞ 1502 02	☞ 1503 10	☞ 1503 13
☞ 1503 15	☞ 1503 16	☞ 1503 19
☞ 1503 20	☞ 1503 21	

15

1532 02

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
1532 02	4	100	300

Packaging:

in bulk, in a cardboard box or a plastic bag