

# LogiLink®

## 4K DisplayPort™ Connection Cable DP male to DP male

Art. No.: CD0100  
CD0101  
CD0102  
CD0103



This DisplayPort connection cable provides you a transmission of 4K Ultra HD resolution video signal from your computer or laptop to a monitor or projector.

### Features:

- » Stable connection, plug and play. This DP to DP cable supports 4K@60 Hz, 2K@165 Hz, 2K@144 Hz, 1080P Full HD and error-free audio channels that are suitable for digital audio channels 7.1, 5.1 and 2
- » With triple shielding and gold-plated connection ensure excellent durability and provide excellent audio and video quality
- » The total bandwidth of HBR2 connections (High Bit Rate 2) is 21.6 Gbps
- » Provides a secure connection with a release button that must be pressed before unplugging
- » Connect your DisplayPort equipped desktop/laptop directly to an HDTV, display, monitor and gaming graphics cards with DisplayPort to stream HD audio and video from your computer to your monitor
- » Perfect for games and expansion workstations



Art-No.	Cable Length	EAN Code
CD0100	1 m	4052792063554
CD0101	2 m	4052792063561
CD0102	3 m	4052792063578
CD0103	5 m	4052792063584



\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.

Made in China

# LogiLink®


## 4K DisplayPort™ Connection Cable DP male to DP male

Art. No.: CD0100  
CD0101  
CD0102  
CD0103



### Specifications:

Connection 1	DisplayPort 20pin, male
Connection 2	DisplayPort 20pin, male
Connector Material	Gold-Plated
Max. Resolution	4K@60 Hz
Supported Bandwidth	21.6 Gbps
Color	Black



### Package Content:

» 1x DisplayPort Connection Cable

### Package Information:

Art-No.	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
CD0100	232x180x20 mm	0.07 kg	440x330x220 mm	100 pcs	7 kg
CD0101	300x193x20 mm	0.113 kg	450x340x280 mm	100 pcs	11.3 kg
CD0102	300x193x20 mm	0.162 kg	440x330x220 mm	50 pcs	8.1 kg
CD0103	300x190x31 mm	0.314 kg	450x340x280 mm	50 pcs	15.7 kg



\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.

Made in China