

Coaxial Cable Connector 16_N-50-10-1/103_U

Description

Right angle cable plug

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

| | |
|--------------------------|--------|
| Impedance | 50 Ω |
| Interface frequency max. | 11 GHz |

Mechanical Data

| | |
|----------------|-----------|
| Centre contact | soldered |
| Outer contact | crimped |
| Weight | 0.0557 kg |

Environmental Data

| | |
|--|------------------|
| Operating temperature | -65 °C to 165 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|-----------------------|--|
| Centre contact | Brass | Gold Plating (without Nickel underplating) |
| Outer contact | Brass | Silver Plating |
| Body | Brass | SUCOPLATE (R) Plating |
| Insulator | PFA / PTFE | |
| Coupling nut | Brass | SUCOPLATE (R) Plating |
| Gasket | VMQ (Silicone rubber) | |
| Crimp ferrule | Copper | SUCOPLATE (R) Plating |

Related Documents

| | |
|----------------------|----------------|
| Outline drawing | DOU-00007517 |
| Catalogue drawing | DOU-00007519 |
| Assembly instruction | DOC-0000182276 |

Ordering Information

| | |
|---------------------|---------------------|
| Bulk 20 pcs package | 16_N-50-10-1/103_UV |
|---------------------|---------------------|

Additional Information

| | |
|-----------------|----------------------------|
| Suitable cables | S_10162_B-11, S_10172_B-11 |
|-----------------|----------------------------|