

# KERN HCN100K200IP

Die Handliche für erhöhte Lasten

**KERN**<sup>®</sup>



## Functions

Data hold function: yes

## Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 35 °C

Minimum ambient temperature: 5 °C

## Power supply

Operating time: 200 h

## Service

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129H

## Category

Brand: KERN

Category: Balances

Product Group: Hanging scale

## Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 150 x 220 x 73 mm

Gross weight: 1,100 kg

Net weight: 800 g

Shipping method: Parcel service

## Construction

Casing material: stainless steel

Dimensions housing (WxDxH): 95 x 180 x 50 mm

## Measuring system

Adjustment options: External calibration

Linearity: 400 g

Precision (of [Max]): 0,005

Readout [d]: 200 g

Recommended adjusting weight: 50 kg (M3)

Reproducibility: 200 g

Resolution: 500

Stabilisation time: 2 s

Warm up time: 10 min

Weighing range [Max]: 100 kg

Weighing system: Strain gauge

Weighing units: kg lb N

## Display

Display digit height: 1,200 cm