



Datasheet

ENGLISH

Stock No: 196-4573

RS Pro MRP440 10 μ F Polypropylene Film Capacitor 440 V ac \pm 10%, Screw Mount 35mm



Product Details

MRP 440 Series

Metallised polypropylene motor run capacitors encapsulated in a non-flammable plastic case which meets the UL specification UL94V0

Particularly suited for motor start, motor run applications with continuous operation

Capacitance tolerance (%)	10
Dissipation factor (@ 50Hz)	< .001
Temperature range (°C)	-25 → +85
Mounting Stud Size	M8x10
Connections	double (¼ inch), terminals suitable for soldering or push-on receptacles



ENGLISH

Specifications:

Capacitance	10 μ F
Voltage	440 V ac
Mounting Type	Screw Mount
Tolerance	\pm 10%
Series	MRP440
Application	1 Phase Induction Motor, 3 Phase Motor
Length	98mm
Dimensions	35 Dia. x 98mm
Dielectric	PLYP
Minimum Operating Temperature	-25°C
Maximum Operating Temperature	+85°C
Tolerance Minus	-10%
Tolerance Plus	+10%