

## Datasheet

# RS Pro 3 $\mu$ F Polypropylene Capacitor (PP) 440 V ac $\pm$ 10% Tolerance MRP440 Series

RS Stock No: 196-4747

## Product Details



### MRP 440 Series

Plastic wire ended metallised polypropylene self heating motor run capacitors  
 Capacitance tolerance (%) 10  
 Dissipation factor (@ 50Hz)  $\leq$  .001  
 Temperature range ( $^{\circ}$ C) -25 to +85  
 Mounting M8x10 stud  
 Wire Ended

## Specification

Capacitance	3 $\mu$ F
Voltage	440 V ac
Tolerance	$\pm$ 10%
Series	MRP440
Application	1 Phase Induction Motor, 3 Phase Motor
Length	56mm
Dimensions	30 (Dia.) x 56mm
Dielectric	PLYP
Capacitor Family	Film
Terminal Type	Screw Mount
Tolerance Plus	+10%
Dissipation Factor	<0.15%

