














Temperature	UFC	Application
675°F/357°C	UFC-6	Temperature Sensitive
775°F/412°C	UFC-7	Most Standard

Please note the above temperatures are the maximum temperatures of the heater. The idle temperature is dependent on the geometry of the cartridge (up to 15°C lower.)

Chisel		
	UFC-6CH5106S UFC-7CH5106S	CARTRIDGE, CHISEL, 0.6mm x 5.1mm
	UFC-6CH9006S UFC-7CH9006S	CARTRIDGE, CHISEL, 0.6mm x 9mm
	UFC-6CH5108S UFC-7CH5108S	CARTRIDGE, CHISEL, 0.8mm x 5.1mm
	UFC-6CH9008S UFC-7CH9008S	CARTRIDGE, CHISEL, 0.8mm x 9mm
	UFC-6CH5112S UFC-7CH5112S	CARTRIDGE, CHISEL, 1.2mm x 5.1mm

Conical		
	UFC-6CN5101S UFC-7CN5101S	CARTRIDGE, CONICAL, 0.13mm x 5.1mm
	UFC-6CN5102S UFC-7CN5102S	CARTRIDGE, CHISEL, 0.2mm x 5.1mm
	UFC-6CN5502R UFC-7CN5502R	CARTRIDGE, CONICAL, BENT, 0.2mm x 5.6mm
	UFC-6CN5504S UFC-7CN5504S	CARTRIDGE, CHISEL, 0.4mm x 5.1mm

	<p>UFC-6CN5504R</p> <p>UFC-7CN5504R</p>	<p>CARTRIDGE, CONICAL, BENT, 0.4mm x 5.6mm</p>
	<p>UFC-6CN8004S</p> <p>UFC-7CN8004S</p>	<p>CARTRIDGE, CONICAL, 0.4mm x 8.0mm</p>

Hoof		
	<p>UFC-6HF5108S</p> <p>UFC-7HF5108S</p>	<p>CARTRIDGE, HOOF, 0.8mm x 5.1mm</p>
	<p>UFC-6HF5112S</p> <p>UFC-7HF5112S</p>	<p>CARTRIDGE, HOOF, 1.21mm x 5.1mm</p>