




FK 209/SA-32  
25 K/W




SOT 32




FK 21 O/SA-CB  
18 K/W




CB (SOT 32 + TO 220)




FK 213/SA-32  
21 K/W




SOT 32




FK 214/SA-CB  
15 K/W




CB (SOT 32 + TO 220)




FK 21 1/32 ...  
25 K/W




SOT 32




FK 212/CB ...  
18 K/W




CB (SOT 32 + TO 220)




FK 215/32 ...  
21 K/W



SOT 32



FK 214/CB ...  
15 K/W



CB (SOT 32 + TO 220)

... bitte gewünschte Oberfläche angeben:

SA = schwarz eloxiert  
MI = lötbare Weißbronze

... please indicate requested surface:

SA = black anodised  
MI = solderable white bronze

... prière d'indiquer la finition:

SA = anodisé noir  
MI = bronze blanc soudable