

TEMPO TA131308



Sample photo

Order symbol: TA131308
Product nbr: 5814041
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074011497
El. number:
Finland: 3438270
:

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		130	130	75	Ingress Protection (EN 60529): IP 65
inch:		5.1	5.1	3.0	Impact Resistance (EN 62262): IK 07
Materials:					Electrical insulation: Totally insulated
Material:		ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 650
Cover screws material:		Polyamide			Certificates:
Cover screws colour:		Grey			
Gasket material:		PUR			
Temperatures:					Fimko
Short term:		-40 ... 80 °C			Gost R
Continuous:		-40 ... 60 °C			
Short term:		-40 ... 175 °F			
Continuous:		-40 ... 140 °F			
Accessories:					
DRM 100		DIN-15 Mounting rail			
MP 1313		Mounting plate			
FP 10674		Wall fastening lug (2 pcs)			
DPS 14553		Grey sealing plug set			

