

ENSTO

SABP101006T

Cubo S enclosure

Code SABP101006T
 GTIN 6438100101640
 ENumber
 Name Cubo S enclosure
 Size 100 x 100 x 60 mm, 50 mm base,
 plain sides, transparent cover, ABS

Description Ensto Cubo S is a series of small to
 medium size enclosures available with
 knockouts or plain sides. The base of the
 enclosures is equipped with unique slots
 for printed circuit boards.

Vendor Ensto Finland Oy



Technical specification

Technical specification

Content: Enclosure base, cover, cover screws,
 mounting screws

Dimensions

Weight: 0.17 kg
 Width: 100 mm
 Size: 100 x 100 x 60
 Height: 100 mm
 Depth: 60 mm
 Inner depth: 45.5 mm
 Outer base depth: 50 mm
 Outer cover height: 10 mm

Temperatures

Operating temperature: -40 ... +60 °C
 Short term temperature range: -40 ... +80 °C

Materials

Base: ABS

| | |
|---------------------|---------------|
| Cover: | Polycarbonate |
| Cover screws: | Polyamide |
| Gasket: | Polyurethane |
| Material selection: | ABS |

Colors

| | |
|--------|------|
| Color: | Grey |
|--------|------|

Mechanical

| | |
|------------------|-------------|
| Impact strength: | IK 07/IK 06 |
|------------------|-------------|

Certificates

| | |
|------------|------------------|
| Standards: | EN 62208, GOST R |
|------------|------------------|

Ratings

| | |
|-----------------------|---|
| Degree of protection: | IP66/IP67 |
| ETIM 7: | EC000261 Enclosure/switchgear cabinet (empty) |

ETIM

ETIM

| | |
|------------------------------|-----------|
| Height: | 100 mm |
| Wall fastening possible: | true |
| Surface finishing: | Untreated |
| Colour: | Grey |
| With mounting plate: | false |
| With glazed door: | true |
| Impact strength: | IK06 |
| Degree of protection (IP): | IP67 |
| Depth: | 60 mm |
| Width: | 100 mm |
| Material: | Plastic |
| RAL-number: | 7035 |
| Suitable for outdoor set-up: | false |

Packaging

Default package

| | |
|---------------|-----------|
| Unit: | PCS |
| Size: | 12 |
| Length: | 385 mm |
| Width: | 260 mm |
| Height: | 130 mm |
| Weight (net): | 1.9824 kg |
| Weight (brt): | 2.2054 kg |
| Volume: | 13.013 |

