

ENSTO

SABP101006G

Cubo S enclosure

Code SABP101006G
 GTIN 6438100101633
 ENumber
 Name Cubo S enclosure
 Size 100 x 100 x 60 mm, 50 mm base,
 plain sides, grey cover, ABS

Description Ensto Cubo S is a series of small to
 medium size enclosures available with
 knockouts or plain sides. The base of the
 enclosures is equipped with unique slots
 for printed circuit boards.

Vendor Ensto Finland Oy



Technical specification

Technical specification

Content: Enclosure base, cover, cover screws,
 mounting screws

Dimensions

Weight: 0.17 kg
 Width: 100 mm
 Size: 100 x 100 x 60
 Height: 100 mm
 Depth: 60 mm
 Inner depth: 45.5 mm
 Outer base depth: 50 mm
 Outer cover height: 10 mm

Temperatures

Operating temperature: -40 ... +60 °C
 Short term temperature range: -40 ... +80 °C

Materials

Base: ABS

Cover:	ABS
Cover screws:	Polyamide
Gasket:	Polyurethane
Material selection:	ABS

Colors

Color:	Grey
--------	------

Mechanical

Impact strength:	IK 07/IK 06
------------------	-------------

Certificates

Standards:	EN 62208, GOST R
------------	------------------

Ratings

Degree of protection:	IP66/IP67
ETIM 7:	EC000261 Enclosure/switchgear cabinet (empty)

ETIM

ETIM

Height:	100 mm
Wall fastening possible:	true
Surface finishing:	Untreated
Colour:	Grey
With mounting plate:	false
With glazed door:	false
Impact strength:	IK06
Degree of protection (IP):	IP67
Depth:	60 mm
Width:	100 mm
Material:	Plastic
RAL-number:	7035
Suitable for outdoor set-up:	false

Packaging

Default package

Unit:	PCS
Size:	12
Length:	385 mm
Width:	260 mm
Height:	130 mm
Weight (net):	1.9824 kg
Weight (brt):	2.2054 kg
Volume:	13.013

