

ENSTO

DABP081209G

Cubo D enclosure

Code DABP081209G
 GTIN 6418677150227
 ENumber
 Name Cubo D enclosure
 Size 80 x 120 x 86 mm, plain sides, grey cover, ABS

Description Ensto Cubo D is a series of small enclosures with plain sides. Special features include fastening pods inside the cover and slots for printed circuit boards in the base.

Vendor Ensto Finland Oy



Technical specification

Technical specification

Content: Enclosure base, cover, cover screws, mounting screws, cover plugs for cover screws

Dimensions

Weight: 0.18 kg
Width: 80 mm
Volume : 82.56 cm³
Size: 80 x 120 x 86
Height: 120 mm
Depth: 86 mm
Inner depth: 72.0 mm
Outer base depth: 71 mm
Outer cover height: 15 mm

Temperatures

Operating temperature: -40 ... +60 °C
Short term temperature range: -40 ... +80 °C

Materials

Base:	ABS
Cover:	ABS
Cover screws:	Stainless steel
Gasket:	Polyurethane
Material selection:	ABS

Colors

Color:	Grey
--------	------

Mechanical

Impact strength:	IK 07/IK 06
------------------	-------------

Certificates

Standards:	EN 62208, GOST R
------------	------------------

Ratings

Degree of protection:	IP66/IP67
ETIM 7:	EC000261 Enclosure/switchgear cabinet (empty)

ETIM

ETIM

Pitched roof:	false
RAL-number:	7035
Material:	Plastic
Surface finishing:	Untreated
Colour:	Grey
Wall build in:	false
With ventilation door:	false
Floor installation possible:	false
Pole fastening:	false
With mounting plate:	false
Impact strength:	IK06
Degree of protection (IP):	IP67
Depth:	86 mm
Tackable:	false
Width:	80 mm
With glazed door:	false
Height:	120 mm
Suitable for outdoor set-up:	false
With backside door:	false
Mounting plate depth-adjustable:	false
EMC-version:	false
Wall fastening possible:	true

Packaging

Default package

Unit:	PCS
Size:	9
Length:	385 mm
Width:	260 mm
Height:	130 mm
Weight (net):	1.665 kg
Weight (brt):	1.888 kg
Volume:	13.013

Pallet package

Unit:	PCS
Size:	567
Length:	1200 mm
Width:	800 mm
Height:	960 mm
Weight (net):	104.895 kg
Weight (brt):	141.944 kg
Volume:	921.6